

TrueOpen Hearing Aid

*First seen
in 135 years*



Zero-Occlusion

Easy Adaption

Noise/Echo cancellation

High Fidelity Sounds

Multi-person conversation

30m Wireless support

Fashion Wearable



TOPlay 聽不累[®]
TrueOpen Hearing Aid

TEL+886-2-22508678

WWW.TOPlay-OGS.com

info@toplay-ogs.com

Winner of Smart Home



COMPUTEX TAIPEI 2013
JURY'S SPECIAL



Specifications

Accessories

HM-8801 TrueOpen Hearing Aid

- Max Gain : 40dB, L & R sides
- Mic : Uni-direction & high-sensitivity,w.mute control
- PDAS sound engine : Noise cancellation & echo suppression, worldwide petent pending
- # of programs : 4 standard modes; customizable.
- # of channels : 10
- Volume : 8-levels L&R,separate/concurrent control
- Wireless support :
Operating freq : 2.4Ghz ISM bands, up to 30m
Attena : 2.5dBi (peak)/PIFA, output power 10dBm
of communication channels : 26
- Battery : 1050mAh rechargeable Lion batt
- Time of Use : 22hrs standalone/11 hrs wireless
- Interfaces :
Mini-USB portx1,for charging/audio-in/prof services
earphone jackx1, Φ 3.5mm hi-fi stereo
- Operation Condition: 5~40°C, Humidity15~93%R.H
- Dimension : L86mm x W48mm x H19mm
- Accessories :
Charging cordx1, MiniUSB*2-to-USB 20cm+20cm
Audio-in cordx1, Φ 3.5mm-to-MiniUSB 100cm
TV adaptorx1, Φ 3.5mm(F)-to-RCA 10cm

HM-8802 Wireless Receiver

- Operating freq : 2.4Ghz ISM band, up to 30m
- Attena : 2.5dBi (peak) /PIFA.
- Volume : 8-levels L&R concurrent +/- control
- Batt : 550mAh rechargeable Lion batt
- Time of Use : up to 9 hrs
- Others: back clip
- Interfaces :
Mini-USB portx1, for charging/prof services
earphone jackx1, Φ 3.5mm hi-fi stereo
- Opertion Condition: 5~40°C, Humidity15~93%R.H
- Dimension : L70mm x W40mm x H22mm



Suitable for :

- Light/ Middle impaired
- Mid-severe impaired
- Middle ear infections

H520 TrueOpen Earphones

- Type : OGS /Comfo Earclips
- Dirve units : Φ 18mm NeoDynamic, 32 Ω
- Freq response : 16~20,000 Hz
- Sensitivity : 98 \pm 3dB at1kHz,Type3.3 emulator
- Cord : back head 22+45cm, or 22+100cm

Leather Pouch Set

